


# NORD GEAR PTE LTD

Member of the NORD DRIVESYSTEMS Group



**NORD GEAR Pte Ltd**  
33 Kian Teck Drive  
Singapore 628850  
Fon +65-6265-9118  
Fax +65-6265-6841  
info.sg@nord.com  
www.nord.com

## GENERAL TERMS AND CONDITIONS

### SECTION 1

The following terms and conditions apply without exception to all our business transactions. Customers' terms of business which deviate from these conditions shall not apply. The following terms shall be defined as follows for the purposes of these General Terms and Conditions:

"**Customer**" shall refer to the customer of Nord Gear Pte Ltd;

"**Conditions**" shall refer to the terms and conditions of this General Terms and Conditions of Nord Gear Pte Ltd;

"**goods**" shall refer to the goods to be delivered by us to the Customer; and

"**we**", "**us**", "**our**" shall refer to Nord Gear Pte Ltd (UEN no.: 199601105K), a private limited company incorporated in Singapore.

### SECTION 2

#### **Conclusion of Contract**

1. The purchase order issued by the Customer is a binding offer by the Customer. We may accept this offer by sending the Customer an order confirmation confirming acceptance of the Customer's purchase order not later than two (2) weeks from the date thereof. Each order so accepted by us shall be upon these Conditions and shall constitute a legally binding contract between us and the Customer and such contract is hereinafter referred to as the "**contract**".

2. All Customer's orders are subject to confirmation by us. For the conclusion of the contract at our discretion, Clause 1 applies accordingly. Any documents attached to the order confirmation by us, such as illustrations, drawings, details

of weights and dimensions and the details in our printed matter are only definitive unless they are explicitly stated as being binding. Unless otherwise stated in writing, descriptions of characteristics, for example in the context of preliminary negotiations, brochures or advertisements do not constitute a warranty as to characteristics or durability nor do they form a part of the contract.

### SECTION 3

#### **Prices**

1. Our quoted prices are valid on an ex works basis (in accordance with Incoterms ® 2020). All prices quoted do not include Goods and Services Tax (GST) or Value Added Taxes (VAT) and such GST or VAT at the prevailing rate shall be added to our quoted prices and shall be reflected in the order confirmation and invoice and shown separately as may be required by law.

2. Unless agreed otherwise, payment is due upon the issuance of our invoice and without discount.

3. For contracts with an agreed term of delivery of more than 4 months, we reserve the right to increase prices in the event of any increases in costs incurred due to increases in the price of materials or supplies or services.

### SECTION 4

#### **Delivery dates, acceptance, transfer of risk**

1. Delivery of the goods shall be on an ex-works basis Incoterms ® 2020, when we place the goods at the disposal of the Customer at the factory of NORD Gear Pte Ltd as named in our order confirmation. Risk of damage to or loss of the goods shall pass to the Customer at the time the goods are placed at the factory of NORD Gear Pte Ltd as named in our order confirmation. Delivery dates are not binding if they are

not explicitly stated as being binding in the order confirmation. The delivery date is complied with on departure from the factory. In the event of delays in delivery arising from causes beyond our control, such as any acts of God or governments, official measures, fires, storms, earthquake, accident, wars, riots, acts of terrorism, strikes, lock-outs, lock downs, pandemics, industrial disputes, global epidemic, shortage of materials or labour, or any acts or omission by you or any third party etc; or delays in delivery by our own suppliers, the agreed delivery dates shall be extended accordingly and we shall not be liable for such a delay in delivery dates or any loss or damage suffered by the Customer as a result thereof. If we are late with delivery of the goods, the Customer shall grant us a reasonable period of grace appropriate to the goods to be supplied. After the expiry of this extended grace period, the Customer may terminate the contract. Compensation in lieu of performance is excluded if the delay in delivery is not due to our deliberate action or our gross negligence.

2. Goods which are ready for dispatch must be accepted by the Customer. If the Customer does not comply with this obligation, we shall be entitled to set a grace period of 2 weeks. After expiry of this grace period we may, at our discretion, terminate the contract or refuse fulfilment of the contract and we as a supplier will be entitled to claim compensation for any losses suffered by us, including but not limited to costs incurred for assembly, disassembly and special material purchased specifically for this order. In any case, costs of storing the goods shall be borne by the Customer and the Customer shall also bear the risks of loss of or damage to the goods until the actual delivery of the goods.

3. In the event that the Customer requires us to bear the costs of such carriage and all the risks of loss of or damage to the goods during such carriage.

4. At the express written request of the Customer, and at the Customer's expense, we shall insure the goods to be delivered against transport risks of all kinds.

5. Packaging will be invoiced at cost. Other agreements require our express written confirmation. If any packing regulations in force at the ma-

terial time (if so applicable) requires that we are obliged to take back the packaging used for transportation, the Customer shall pay the costs for the return transport of the packaging used.

## **SECTION 5**

### **Reservation of Title**

1. We retain title in all goods supplied by us until settlement of each and every claim under every contract entered into between us. In the case of current invoices, the reserved goods shall be deemed to be security against our claims for the balance payment.

2. As long as the Customer is not in arrears of payment to us, he may sell the goods in the course of normal business under the usual conditions. For the securing of all our claims from the business relationship, the Customer hereby assigns to us all the Customer's claims to the sales proceeds resulting from the resale of the goods. We accept this assignment of claims. The Customer shall advise us of the claims assigned to us, provide notice to the relevant debtors of such assignment and provide us with all necessary information to enable us to effect collection on such claims. We hereby authorise the Customer to collect such claims on our behalf, such authorisation to be revoked at our absolute discretion.

3. Processing or restructuring by the Customer of the goods which we have delivered is always performed on our behalf and subject to our retention of title in the goods as per Clause 1 of Section 5 above. If the goods are processed together with other goods which are not our property, we acquire a co-ownership of the new article in relation to the value of our goods to the other processed goods at the time of processing.

4. The exercise of reservation of title does not constitute a termination of the contract.

---

## **SECTION 6**

### **Warranty**

1. The Customer is obliged to immediately inspect the goods delivered by us for faults and report any faults to us, within 7 working days after receipt of the goods. This also applies in the case that a different good or a wrong quantity was delivered. Any delay in submission of complaints of faults or of wrong quantity normally shall result in an exclusion of warranty.

2. At our discretion, in the case of faults recognised by us, we shall provide rectification of the fault free of charge (reworking) or the delivery of replacement good(s) which are free of faults (subsequent delivery). If a total of 3 attempts at reworking or subsequent deliveries are fruitless or ineffective, the Customer may terminate the contract or demand a reduction in price.

3. Further claims by the Customer, in particular claims for compensation, including loss of profits or other damage to the Customer's assets are expressly excluded.

4. If an obligation essential to this contract is breached by us due to negligence, our liability is restricted to the foreseeable damage resulting from such breach of obligation.

5. For faults that are not possible to detect within the said 7 working days as per Clause 1 of Section 6 above, such faults shall be reported immediately in writing to us once they are discovered. The warranty period is one year from the delivery of the goods. The warranty period counts from the date of delivery. The warranty period for any repaired or replaced good which is delivered to the Customer shall be the unexpired remaining portion of the abovementioned warranty period.

6. Warranty claims are excluded if the fault is due to one of the following causes: Unsuitable or incorrect use; excessive loads; incorrect installation or commissioning; natural wear; operation at conditions deviating from those specified in the order confirmation; mal-operation; inappropriate operating media; substitute materials; use of oils or greases not approved by us; mechanical, chemical, physical, electromechanical, electro-

chemical and/or electrical influences; interference by third parties. Warranty claims are furthermore excluded if the Customer undertakes reworking, modifications or repairs without granting us the opportunity for reworking, or without obtaining our written consent.

7. Transportation and packaging costs for the goods complained of and reworked or delivered in replacement shall be at the expense of the Customer.

8. Except for the express representations and warranties set out herein, we do not make any other express or implied representations or warranties, in fact or in law, including without limitation any express or implied warranties of quality or fitness for a particular purpose. Except as expressly provided herein, all representations, warranties, terms, conditions, undertakings or inducements, whether express, implied, statutory, under common law or otherwise relating in any way to the goods are hereby excluded to the fullest extent permitted by law.

9. We will not accept any responsibility relating to the suitability of our goods where inaccurate or incomplete information has been provided by the Customer.

## **SECTION 7**

### **Copyright/Intellectual property**

We reserve all intellectual property rights and copyright in and to illustrations, drawings, samples and other documents provided by us to the Customer. The Customer is solely entitled to their utilisation thereof according to the contract. Any further use or utilisation, in particular the transfer to third parties shall require our prior written consent.

## **SECTION 8**

### **General Provisions and Applicable Law**

1. Amendments and supplements must be made in writing and agreed upon by the authorised representatives of each of the parties. This also applies to the amendment of this clause which shall require the written form.

2. The invalidity, illegality or unenforceability of any part of these Conditions under the laws of any jurisdiction shall not prejudice the validity, legality or enforceability of the remaining provisions herein and these Conditions shall continue in force save that such provision deemed to be invalid, illegal or unenforceable shall be excised from these conditions.

3. The Customer shall not without our prior written consent assign transfer or sub-contract the rights or obligations under these Conditions or any part thereof to any third party. We may assign transfer or sub-contract these Conditions or any part thereof to any third party.

4. These Conditions shall be governed and construed in accordance with the laws of Singapore.

5. The Customer and us hereby agree to submit to the non-exclusive jurisdiction of the Singapore courts.

6. A person or entity who is not a Party to the agreement between us and the Customer shall have no right under the Contracts (Rights of Third Parties) Act (Cap. 53B) to enforce any term of the agreement, regardless of whether such person or entity has been identified by name, as a member of a class or as answering a particular description.

Edition: 16<sup>th</sup> June 2020