

GETRIEBEBAU NORD

Member of the NORD DRIVESYSTEMS Group



Getriebebau NORD GmbH & Co. KG

Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com

SK TIE4-M12-ASI-AUX

Part number: 275 274 513

AS interface with auxiliary power connection extension

M12 BUS system connector



Scope of delivery

1 x	M12 Plug connector	SK TIE4-M12-ASI-AUX
1 x	Cover cap	yellow

As-delivered status with screwed-on connector cover



Field of use

The M12 Plug connector has open cable ends and wire end sleeves. It is used to make a pluggable connection using normal commercial M12 round plug connectors. It connects the AS Interface technology option with the incoming AS Interface field bus cable at the input side.

Technical data

Version	
Temperature range	-30 ... +90 °C
Contact insert Colour / Material	Yellow / RAL 1018 Plastic
Round plug connector Material	Metal, CuZn, nickel plated
Connection / Type Round plug connector	M12x1, adjustable Plug connector with flexible strand M16x1.5, metric screw thread
Contact set Contacts / Coding	5 pin, A - coded

Weight	23 g
Connector cover Colour / Material	Yellow / RAL 1018 Plastic
Protection class (screwed)	IP67
Fastening	Hexagonal nut M16x1.5 *
Tightening torques *	
M12x1 Socket connector	0.6 Nm
M16x1.5 Screw thread	1.5 Nm


* Suitable assembly spanner commercially available (see Installation)

Cable	
Number of conductors / Cross section	4 x 0.34 mm ²
Wire strands / colours	UL / (br, bl)
Length of wire strands	250 mm
Degree of fouling	3 / 2

Mech. Service life	min. 100 plugging cycles
Operating voltage	max. 250 V
Current rating	4 A
Insulation resistance	≥ 10 ⁸ Ω

Technical Information / Datasheet	SK TIE4-M12-ASI-AUX			
Connection extension	TI 275274513	V 1.3	3021	en

Circuit diagram






NOTICE

Validity of this document

This document is only valid in combination with the operating instructions for the relevant electronic drive technology and under strict compliance with the safety and warning instructions which they contain. Safe commissioning of this module and the electronic drive technology depends on the availability of this information.

Installation / option locations











The M12 Receptacle connector are intended for direct installation in a free M16 hole / threaded opening of the device series (see below).


Device series	Recommended option location	Option locations
SK 135E * SK 180E * ... SK 190E * Housing SK 1xxE xxx-xxx-x (-C)	4R / 4L (incoming) 5R / 5L (outgoing)	
SK 200E Frequency inverter connecting unit SK TI4-x-2xx-x (-C)	4R / 4L (incoming) 5R / 5L (outgoing) optional ** 6R / 6L, 7R / 7L, 8R / 8L	
BUS technology box BUS connection unit SK TI4-TU-BUS (-C)	1 / 2 / 3 / 4 optional *** 5R / 5L	
<p>* The configuration capability of the respective Receptacle connector depends on its functionality with regard to the device series, e.g. the SK TIE-M12-SH-IN M12 male connector cannot be installed with the SK 1xxE housing.</p> <p>** Size 1 – 3 with optional SK TIE4-M12-M16 connection extension, size 4 direct installation</p> <p>*** With optional SK TIE4-M20-M16 connection reduction</p>		

The installation position and mounting location (coding pin or coding groove on contact carrier) of the Socket connector is freely positionable and should be aligned (see installation step 6) such that angled M12 round connectors can also be connected in a way that avoids collisions.

The installation steps described in the following apply to the installation of the M12 Receptable connectors in the housing and in the frequency inverter connecting unit or the BUS connecting unit of an external technology box.

Installation steps for installation of the M12 Receptable connector

<p>1.</p>	<p>Remove M16 blind plug at the provided option location side (right / left) of the starter or frequency inverter housing or the connection unit.</p>	
	<p>Remove M16 blind plug from the provided option location hole (bottom) of the BUS connection unit.</p>	
<p>2.</p>	<p>Screw the middle hexagonal nut towards the front using a size 17 open-ended spanner.</p> 	
<p>3.</p>	<p>EMC Twist associated wire pairs together (e. g. bus system, power supply, etc.).</p>	
<p>4.</p>	<p>Screw M12 flanges component directly into the affected M12 threaded opening of the housing or connecting unit of the frequency inverter. Screw M12 Receptable connector into the relevant M16 threaded opening of the BUS connecting unit.</p>	
<p>Alternative option locations Connection extension SK TIE4-M12-M16 The M12 Receptable connector can alternatively be installed with an optional M12-M16 connection extension. First screw the M12 Receptable connector directly into the connection extension and then fit into the M12 threaded opening in the connection unit. For more information see Optional accessories</p>		
<p>Connection reduction SK TIE4-M20-M16 The M12 Receptable connector can alternatively be installed with an optional M20-M16 connection reduction. First screw the M12 Receptable connector directly into the connection reduction and then fit into one of the side M12 threaded openings in the connection unit. For more information see Optional accessories</p>		
<p>5.</p>	<p>Align coding pin / coding groove vertically to 12 o'clock by rotating the front hexagonal nut.</p>	<p>Socket connector Plug connector</p> 
<p>6.</p>	<p>Secure the front hexagonal nut with a 17 mm open-ended spanner. Screw the rear hexagonal nut to the connection unit or the starter or frequency inverter housing using a size 17 open-ended spanner or a special torque / installation wrench. Take the specified tightening torques into consideration, see technical data.</p>	

7.	Ensure that the M12 round plug connector or the cover cap is properly screwed onto the M12 Receptable connector and tightened.	
----	--	---

NOTICE

Corrosion

Pay attention to leaktightness during the installation of all components (assembly, connection extension etc.). It must be ensured that all components are correctly seated, and the tightening torques are adhered to when doing this.

Failure to do this will allow moisture to penetrate the device, which will result in the risk of corrosion and short circuiting.

- In order to ensure that protection class **IP66** is complied with (concerns all devices with type key SK ...-C), another pressure - **leaktightness** test must be performed when the assembly work has been completed.

Information

Torque / assembly wrench



In order to provide a secure, sealed and vibration-proof connection, the M12 connection extensions, which are equipped with a hexagonal threaded ring (size 17), should be tightened with special torque / assembly wrenches. For professional installation NORD recommends the use of commercially available assembly tools (M12, size 17) with an adjustable, defined tightening torque (e.g. from Murrelektronik).

Information

NOTE:

When installed, the following **yellow** connection extensions / plugs look identical.

Designation	Part number
SK TIE4-M12-SH-IN	275274519
SK TIE4-M12-ASI	275274502
SK TIE4-M12-ASI-AUX	275274513



Heed the correct assignment to functions when installing the different types in a connection unit / housing and mounting / connecting the function-specific M12 round plug connectors!

Connections

The open cable ends of the extension / M12 Plug connector are connected to the terminal strip of the BUS connection unit (technology box), the BUS customer interface or the control terminal strip in the frequency inverter or the motor starter (see below).



**Frequency inverter
and motor starter**



**BUS connection unit
SK TI4-TU-BUS (-C)**




**BUS technology box
(SK TU4-... (-M12) / (-C))**

Electrical connections



Contact assignments
4-pole
Plug connector
A-coded



**Connection extension
M12 Plug connector
SK TIE4-M12-ASI-AUX**

Pin	Colour	Signal	Contact	Designation
1	brown	ASI +	84	ASI +
2	white	GND	40	GND
3	blue	ASI -	85	ASI -
4	black	+24 V	44	+24 V

**Connecting terminals
SK 1x5E (set jumper
position at device)
SK 22xE/ 23xE-...-AxB**



Optional accessories

 Information

M12 / M20 screw openings



Conductive connection extensions made from brass SK TIE4 M12 M16 from M12 to M16 or connection reductions SK TIE4 M20 M16 from M20 to M16 are optionally available for installing the M12 connection extensions in an M12 or M20 screw opening.

For more information, see further documentation.

Further documentation (www.nord.com)

Dokument	Bezeichnung
BU 0090	AS-Interface (SK 300E ... SK 750E)
BU 0135	Motor starter manual SK 105E ... SK 175E
BU 0180	Frequency inverter manual SK 180E, SK 190E
BU 0200	frequency inverter manual SK 2xxE
TI 275280000	Bus connection unit SK TI4-TU-BUS
TI 275280500	Bus connection unit SK TI4-TU-BUS-C
TI 275274510	Connection extension SK TIE4-M12-M16
TI 275274511	Connection reduction SK TIE4-M20-M16
TI 275274502	Connection extension SK TIE4-M12-ASI